

# Installation Instruction


## Cartridge for 600 Series

To ensure that your installation proceeds smoothly.  
Please read these instructions carefully  
before installation.

Round Handle




Lever Handle



Certificated to comply with ASME  
A112.18.1 / CSA B125.1 & ASSE 1016 /  
ASME A112.1016/ CSA B125.16

## Recommended Tools:




Adjustable Wrench




Channel Locks

## Lever Handle Installation



## Round Handle Installation



Remark: 1. Use With A Spline D Post Adapter Inside The Handle